

SF-P016

Behaviour of nitrided layer formed on S45C carbon steel during gaseous nitriding

손석원, 유광춘, 이원범*

Heat treatment R&D group, Korea Institute of Industrial Technology

재료의 표면 강화 방법 중의 하나인 질화공정을 이용하여 탄소강 S45C 소재의 질화 거동에 대하여 연구하였다. 520°C 온도에서 질화 공정을 진행하여 공정시간에 따른 Kn값을 수소 센서로 측정하여 공정시간에 따른 N-potential의 변화와 그에 따른 화합물층 성장 및 화합물층의 상변화에 대해 관찰하였다. 화합물층의 미세구조 변화는 광학현미경 및 주사전자현미경을 통해 관찰하였다. 가스 질화 처리 후 표면경도는 약 600Hv의 정도값이 측정되었고, 공정 시간이 늘어남에 따라 화합물층 및 경화깊이가 증가되고 표면 화합물이 성장하여 porous가 감소하는 것을 확인 할 수 있다. 경화깊이는 1440분 일 때 약 0.5mm 경화깊이를 얻었고, 화합물층의 성장은 ϵ 상(Fe₂-3N)과 γ '상(Fe₄N)으로 두 개의 상으로 형성되는 것을 관찰할 수 있었다. 시험 결과를 바탕으로 S45C 소재의 탄소 함량에 따른 lehrer diagram을 열역학 적으로 계산하고 화합물층의 형성 기구에 대해 비교 분석하였다.

Keywords: Gas Nitriding, Nitriding potential, Compound layer, Carbon steel S45C

SF-P017

Impedance-Based Characterization of 2-Dimensional Conduction Transports in the LaAlO₃/Sr_xCa_{1-x}TiO₃/SrTiO₃ systems

Yoo-Jin Choi¹, Da-Hee Park¹, Eui-Hyun Kim¹, Chan-Rok Park¹, Kyeong-Woo Kwon¹,
Seon-Young Moon², Seung-Hyub Baek², Jin-Sang Kim², and Jinha Hwang¹

¹Dept. of Mat. Sci. and Eng., Hongik University, Seoul 121-791, South Korea,

²Electronic Materials Center, Korea Institute of Science and Technology, Seoul 02792, South Korea

The 2-dimensional electron gas (2DEG) layers have opened tremendous interests in the heterooxide interfaces formed between two insulating materials, especially between LaAlO₃ and SrTiO₃. The 2DEG layers exhibit extremely high mobility and carrier concentrations along with metallic transport phenomena unlike the constituent oxide materials, i.e., LaAlO₃ and SrTiO₃. The current work inserted artificially the interfacial layer, Sr_xCa_{1-x}TiO₃ between LaAlO₃ and SrTiO₃, with the aim to controlling the 2-dimensional transports. The insertion of the additional materials affect significantly their corresponding electrical transports. Such features have been probed using DC and AC-based characterizations. In particular, impedance spectroscopy was employed as an AC-based characterization tool. Frequency-dependent impedance spectroscopy have been widely applied to a number of electroceramic materials, such as varistors, MLCCs, solid electrolytes, etc. Impedance spectroscopy provides powerful information on the materials system: i) the simultaneous measurement of conductivity and dielectric constants, ii) systematic identification of electrical origins among bulk-, grain boundary-, and electrode-based responses, and iii) the numerical estimation on the uniformity of the electrical origins. Impedance spectroscopy was applied to the LaAlO₃/Sr_xCa_{1-x}TiO₃/SrTiO₃ system, in order to understand the 2-dimensional transports in terms of the interfacial design concepts. The 2-dimensional conduction behavior system is analyzed with special emphasis on the underlying mechanisms. Such approach is discussed towards rational optimization of the 2-dimensional nanoelectronic devices.

Keywords: 2DEG, LaAlO₃, SrTiO₃